

Return Filters - Standard

RFL-170 · RFL-230

In-line mounting · Connection G1¼ / -20 SAE · Nominal flow rate up to 290 l/min / 77 gpm





In-line Return Filter RFL-170

Description

Application

In the return line circuits of hydraulic systems.

Filter maintenance

By using a clogging indicator the correct moment for maintenance is stated and thus the optimum utilization of the filter life is guaranteed.

Materials

Filter head: Aluminum alloy

Filter bowl: Polyamide, GF reinforced Seals: NBR (FPM on request)

Filter media: EXAPOR®Standard - inorganic multi-layer

microfiber web

Paper - cellulose web, impregnated with resin

Accessories

Electrical and optical clogging indicators are available on request. For technical data and dimensions see datasheet 60.20.

Characteristics

Nominal flow rate

Up to 290 l/min / 77 gpm.

The nominal flow rates indicated by ARGO-HYTOS Standard are based on the following features:

- ➤ Closed by-pass valve at $v \le 150 \text{ mm}^2/\text{s} / 698 \text{ SUS}$
- Element service life > 500 operating hours at an average fluid contamination of 0.07 g per l/min / 0.27 g per gpm flow volume
- > Flow velocity in the connection lines \leq 6 m/s / 20 ft/s

Connection

Threaded ports according to ISO 228 or DIN 13 and SAE standard J514. Sizes see Selection Chart, page 3, (other port threads on request).

For installation recommendations, see info sheet 00.325.

Filter fineness

10 μm(c) ... 30 μm(c)

B-values according ISO 16889 (see diagrams).

Hydraulic fluids

Mineral oil and biodegradable fluids (HEES and HETG, see info-sheet 00.20).

Temperature range

-30 °C ... +100 °C (temporary -40 °C ... +120 °C) -22 °F ... +212 °F (temporary -40 °F ... +248 °F)

Operating pressure


Max. 10 bar / 145 psi


Mounting position


Vertical mounting to be preferred, filter head on top.

www.argo-hytos.com

Dimensions








Measurements

Type [mm]	Α	В		С	D	Ε	F	G	Н	T	K		L	M Ø / depth	N	0	Q		RS	Т
RFL-170	G11/4	G1	1/4	52	192	28	85	133	117	60	AF 41	4	17.6	M8 / 15	100	AF 55	31.	5 13	33 14	38.1
RFL-230	G11/4	G1	1/4	52 3	302	28	85	133	117	60	AF 41	4	17.6	M8 / 15	100	AF 55	31.	5 13	33 14	38.1
Type [inch]	А			В	C		D	E	F	(i I	1	I	K	L	M Ø / de _l	oth	N	O mm	Q
RFL-170	-20 SA	Æ*	-20	SAE*	2.0)5	7.56	1.12	3.35	5.2	23 4.	60	2.36	5 AF 41	1.87	M8 / 0	0.6	3.94	AF 55	1.24
RFL-230	-20 SA	Æ*	-20	SAE*	2.0)5	11.89	1.12	3.35	5.2	23 4.	60	2.36	5 AF 41	1.87	M8 / 0	0.6	3.94	AF 55	1.24
Туре	R			S	Т	-														

Type [inch]	R	S	Т						
RFL-170	5.24	0.55	1.5						
RFL-230	5.24	0.55	1.5						

^{*}Corresponds to 1 $^{5}/_{8}$ - 12 UN - 2B

Symbol




Page 100 www.argo-hytos.com

Filter assembly

Order example:

RFL - 230 - UE - N3 - KM - 100




Filters delivered with 2 plugged connections M12 x 1.5 for clogging indicators.


Spare filter element

Order example:

P3.1025-01



Spare parts




Pos.	Designation	Part No.
1	Replacement filter element	see above
2	O-ring 115 x 4.5 mm 4.53 x 0.18 inch	N007.1155
3	Filter bowl RFL-170	D 230.0102
3	Filter bowl RFL-230	D 230.0101

The functions of the complete filters as well as the outstanding features of the filter elements assured by ARGO-HYTOS can only be guaranteed if original ARGO-HYTOS spare parts are used.

www.argo-hytos.com Page 101


∆p-curves for complete filters

Pressure drop as a function of the **flow volume** at $v = 35 \text{ mm}^2/\text{s} / 162 \text{ SUS } (0 = \text{housing empty})$



Filter fineness curves

Filtration ratio β as a function of particle size x obtained by the Multi-Pass-Test according to ISO 16889



The abbreviations represent the following β -values resp. finenesses:

For EXAPOR®Standard and Paper elements:

 $\begin{array}{llll} 10 \text{EXS} &=& \overline{\beta}_{10 \text{ (c)}} &=& 200 & \text{EXAPOR} \\ 16 \text{EXS} &=& \overline{\beta}_{16 \text{ (c)}} &=& 200 & \text{EXAPOR} \\ 30 \text{P} &=& \overline{\beta}_{30 \text{ (c)}} &=& 200 & \text{Paper} \\ \end{array}$

Based on the structure of the filter media of the 30P paper elements, deviations from the printed curves are quite probable.

For special applications, finenesses differing from these curves are also available by using special composed filter material.

Quality Assurance

Quality management according to DIN EN ISO 9001

To ensure constant quality in production and operation, ARGO-HYTOS filter elements undergo strict controls and tests according to the following ISO standards:

ISO 2941 Verification of collapse / burst pressure rating
ISO 2942 Verification of fabrication integrity (Bubble Point Test)
ISO 2943 Verification of material compatibility with fluids
ISO 3968 Evaluation of pressure drop versus flow characteristics
ISO 16889 Multi-Pass-Test (evaluation of filter fineness and dirt-holding capacity)
ISO 23181 Determination of resistance to flow fatigue using high viscosity fluid

Various quality controls during the production process guarantee the leakfree function and solidity of our filters.

Illustrations may sometimes differ from the original. ARGO-HYTOS is not responsible for any unintentional mistake in this specification sheet.

Page 102 www.argo-hytos.com